HPHT Consistometer Model 422 Single Cell

Description

Fann Consistometer Model 422 (single cell) is specifically designed to measure the thickening time of cement slurries in strict compliance with ISO requirements and API specifications. With high temperatures and pressures applied to the cement, it is possible to simulate a variety of conditions found in actual down-hole well cementing. This model has been tested to temperatures up to 400°F and pressures up to 22,000psi.

This pressurized consistometer has all of the operational controls conveniently located on the front panel. The readout indicators for the viscosity, pressure, and temperature, as well as operational instructions, are easily read from the 12-inch color touch-screen. The consistometer is designed for closure, heating, and pressurization to be achieved quickly. This ensures compliance with the requirement of API schedules. The temperature control system automatically controls the rate of temperature rise of the slurry (i.e. temperature gradient). When the slurry reaches the desired maximum temperature, the system will hold the slurry temperature at that level. The temperature and viscosity of the slurry, and current pressure



are displayed constantly on the touch-screen numerically and graphically. Contains easy spin-on/ off automotive style mineral oil filter and 100 micron high pressure filter to remove sediment and other contaminants from mineral oil.

Advantages

- Easy network LAN for remote viewing in real-time
- USB data export
- Precision magnetic drive assembly
- Automatic cooling
- No other computer required to operate the system
- Onboard memory to store thousands of tests' data
- Supplied with tool kit, spares, and accessories
- Pressure control option can be added
- Redesigned with automated functions
- Oil reservoir cooling
- 12in color touchscreen display

- Rate of temperature rise of the slurry can be closely controlled over a wide range of temperature gradients including a multi-slope gradient
- The cooling coils around the pressure vessel permits the circulation of a cooling fluid to cool the pressure vessel quickly
- High-wattage slurry heater provides high heating rates needed to simulate high temperature gradients in wells
- Viscosity alarms can be set over the range from less than 30 Bc to 100 Bc





SA	AED TEST PROFILES	▼ Select o	r Save Customer
LOAD PROFI	LE DELETE PROF	ILE NEW CUSTOM	IER DELETE CUSTOME
SAVE CU	RRENT TEST PROFILE	ADDITIONA	AL TEST INFORMATION
TEMPERATURE	C ITOUCH GRAPH	TO CHANGE RAMP VAL	UESĮ
00			
80			
60			
40			
20			
0 20 40	60 80 100 120 140 16	0 180	
DIPTOLOT			SAVE & EXIT
DISTRICT	CEMEN	YIELD	SAVE & EXIT
WELL	WATER	DENSITY	CANCEL

Specifications

	1	
Electrical		
Input Voltage	230 VAC (±10%)	
Input Power	6500 W	
Current	30 A	
Input Frequency	50-60 Hz	

Dimensions	
Height	61 in. (155 cm)
Width	33 in. (84 cm)
Depth	30 in. (76 cm)
Weight	850 lbs. (386 kg)

Air/Water Connections		
Water In/Out	1/4 MNPT (2)	
Air Input	1/4 MNPT (1) (Max 120psi)	

Drive Unit	
Drive Unit	.65A, 180VDC
Drive Speed	150 rpm (Variable Speed Optional)

Heater		
Heater Power	5000 W	
Heater Type	Internal Cast Rod Heater	
Heater Control	SS Relay	

Environmental			
Operating Temperature	32 -105 °F (0 - 40 °C)		
Operating Humidity	0 - 95% non-condensing		

Ordering Information

Part No. 102538934 - Single Cell HPHT Pressurized Consistometer 22,000psi 400°F Model 422

Fann Instrument Company offers a complete line of equipment, materials, and supplies for analyzing various drilling fluids and oil well cements in accordance with API Specifications and API Recommended Practices.

